


SPECTRALON® DIFFUSE REFLECTANCE STANDARDS

High Lambertian reflectance over their effective spectral range

HEMISPHERICAL SPECTRAL REFLECTANCE FACTORS FOR SPECTRALON STANDARDS



CONSISTENT

All reflectance calibration tests are performed in the Reflectance Spectroscopy Laboratory at Labsphere. The standards used in these tests are directly traceable to the National Institute of Standards and Technology (NIST).

Spectralon Diffuse Reflectance Standards are available individually and in sets, consisting of a diffuse white standard and a selection of diffuse gray standards. Each standard is supplied with complete diffuse reflectance data from 250 - 2500, every 50 nm. All standards are housed in a durable delrin holder with a protective cover.

ACCURATE

Spectralon® Diffuse Reflectance Standards can offer the highest diffuse reflectance values of any known substance. These durable, chemically inert standards can have typical reflectance values ranging from 2% to 99% and are spectrally flat over the UV-VIS-NIR spectrum. All Spectralon materials are optically flat to +/- 4% over the range of 250 - 2500 nm and +/- 1% over the photopic region of the spectrum.

Spectralon Diffuse Reflectance Standards are highly Lambertian, with Spectralon SRM-99 reflectance material being the most Lambertian reflector available for use over the wavelength range from 250 - 2500 nm.

CALIBRATE:

- Densitometers
- Integrating Sphere Systems
- Optical Equipment
- Photographic Equipment
- Reflectometers
- Remote Sensing Instruments



Specifications

Set Part Numbers	Standards Included	Order Numbers	Reflectance Factor	Reflective Area (Inches)	Dimensions (Inches)
RSS-04-010		AS-01163-060			
	SRS-99-010	AS-01160-060	99%	1.25 D	1.50 D x 0.55 H
	SRS-75-010	AS-01160-260	75%	1.25 D	1.50 D x 0.55 H
	SRS-50-010	AS-01160-460	50%	1.25 D	1.50 D x 0.55 H
RSS-04-020		AS-01161-960	2%	1.25 D	1.50 D x 0.55 H
		AS-01165-060			
	SRS-99-020	AS-01161-060	99%	2.00 D	2.38 D x 0.60 H
	SRS-75-020	AS-01161-260	75%	2.00 D	2.38 D x 0.60 H
RSS-08-010		AS-01161-460	50%	2.00 D	2.38 D x 0.60 H
		AS-01161-960	2%	2.00 D	2.38 D x 0.60 H
		AS-01163-160			
	SRS-99-010	AS-01160-060	99%	1.25 D	1.50 D x 0.55 H
RSS-08-020	SRS-80-010	AS-01160-160	80%	1.25 D	1.50 D x 0.55 H
	SRS-60-010	AS-01160-360	60%	1.25 D	1.50 D x 0.55 H
	SRS-40-010	AS-01160-560	40%	1.25 D	1.50 D x 0.55 H
	SRS-20-010	AS-01160-660	20%	1.25 D	1.50 D x 0.55 H
	SRS-10-010	AS-01160-760	10%	1.25 D	1.50 D x 0.55 H
	SRS-05-010	AS-01160-860	5%	1.25 D	1.50 D x 0.55 H
	SRS-02-010	AS-01160-960	2%	1.25 D	1.50 D x 0.55 H
		AS-01165-160			
	AS-01161-060	99%	2.00 D	2.38 D x 0.60 H	
	AS-01161-160	80%	2.00 D	2.38 D x 0.60 H	
	AS-01161-360	60%	2.00 D	2.38 D x 0.60 H	
	AS-01161-560	40%	2.00 D	2.38 D x 0.60 H	
	AS-01161-660	20%	2.00 D	2.38 D x 0.60 H	
	AS-01161-760	10%	2.00 D	2.38 D x 0.60 H	
	AS-01161-860	5%	2.00 D	2.38 D x 0.60 H	
	AS-01161-960	2%	2.00 D	2.38 D x 0.60 H	

Diffuse Reflectance Standard Sets

Diffuse Reflectance Standards are available in sets of four or eight standards in either 1.25 or 2.00 inch diameters. A set of four standards includes one each of the following reflectance values: 99%, 75%, 50% and 2%. A set of eight standards includes one each of the following reflectance values: 99%, 80%, 60%, 40%, 20%, 10%, 5% and 2%.

Individual Diffuse Reflectance Standard

Diffuse Reflectance Standards are available individually (1.25 or 2.00 inch diameter) in the following reflectance values: 99%, 80%, 75%, 60%, 50%, 40%, 25%, 20%, 10%, 5% and 2%.

Custom Reflectance Standards

Spectralon Diffuse Reflectance Standards are available on custom order with reflectance properties to meet your specific needs. Please contact our Technical Sales Department for details.