


SPECTRALON® DIFFUSE COLOR STANDARDS

Highly stable, durable Color standards for calibrating colorimeters and spectrophotometers



RELIABLE

Made of Spectralon Diffuse Reflectance material, these color standards offer exceptional reflectance properties that are nearly perfectly Lambertian. Unlike ceramic tiles, Spectralon is independent of viewing geometry.

The reflectance of Spectralon Color Standards is extremely consistent and reproducible. This quality helps eliminate gross margins of error in manufacturing processes of color-dependent products such as paints or inks.

The high thermal stability of Spectralon Color Standards eliminates the need to rigorously control the temperature in the laboratory. The slight color change of the standards with increasing temperature is extremely gradual and can be easily monitored.

Spectralon color standards are durable, washable and easily machined without loss of color or surface texture. The standards retain uniformity throughout, despite daily exposure to harsh environments.

Labsphere can produce custom color standards to meet your individual needs. Spectralon Color Standards are available either calibrated or uncalibrated, in a variety of configurations.

FEATURES:

Highly diffuse, eliminating errors due to viewing angle

Consistent reflectance to eliminate gross margins of color-dependent products

Thermally stable for a wide range of environment conditions

Durable, washable, and waterproof

Data includes tristimulus values, chromaticity coordinates, UCS coordinates, and CIELAB and CIELUV values.

Available calibrated or uncalibrated, in 1.25 or 2-in. diameters, and in multiple configurations

Colors include red, green, blue, yellow, cyan, orange, purple, and violet

BEST FOR MEASURING:

LED Sourced Systems

Solid State Lighting

Large Area LED Display

Backlighting

General Lighting

Automotive Lighting

Architectural Lighting

EASY-TO-USE

Spectralon Diffuse Color Standards aid in developing consistent color reproduction for manufacturers of products such as textiles, papers, pharmaceuticals, paints and inks. These color standards provide highly stable, reproducible spectral reflectance.

As opposed to ceramic color tiles, which are characterized by a specular surface, Spectralon color standards are highly diffuse, thus simplifying measurement procedures by removing the effect of viewing geometry. Spectralon color standards are durable and maintain a consistent reflectance over time.

These properties - Lambertian behavior, durability and stability - make Spectralon Diffuse Color Standards the ideal choice for calibrating colorimeters and spectrophotometers.

Data includes tristimulus values, chromaticity coordinates, UCS coordinates, and CIELAB and CIELUV values.



Specifications

Part Number	Order Number	Number of Colors	Number of Neutrals	Reflective Area (inches)	Description
CSS-04-010	AS-01170-060	4	0	1.25 D	red, green, blue, yellow
CSS-04-020	AS-01178-060	4	0	2.00 D	red, green, blue, yellow
CSS-04A-010	AS-01170-160	4	0	1.25 D	cyan, orange, purple, violet
CSS-04A-020	AS-01178-160	4	0	2.00 D	cyan, orange, purple, violet
CSS-08-010	AS-01170-260	4	4	1.25 D	red, green, blue, yellow, 99%, 50%, 20%, 2%
CSS-08-020	AS-01178-260	4	4	2.00 D	red, green, blue, yellow, 99%, 50%, 20%, 2%
CSS-08A-010	AS-01170-360	8	0	1.25 D	red, green, blue, yellow, cyan, orange, purple, violet
CSS-08A-020	AS-01178-360	8	0	2.00 D	red, green, blue, yellow, cyan, orange, purple, violet
CSS-12-010	AS-01171-060	8	4	1.25 D	above eight colors and 99%, 50%, 20%, 2%
CSS-12-020	AS-01179-060	8	4	2.00 D	above eight colors and 99%, 50%, 20%, 2%